

# SMART SEAL LINER

## SAFR / SADT / SBFR

**SAFR** rings begin 12.5 cm from the center of the distal end.

**SBFR** rings begin 7.5 cm from the center of the distal end.

**SADT** rings for:

- Sizes 20-28 begin 7.5 cm from the center of the distal end.
- Sizes 32-38 begin 12.7 cm from the center of the distal end.



## DESCRIPTION

The ALPS™ Smart Seal Liner features raised bands that grip the socket wall to form a secure interface. The low modulus bands stretch against the socket wall, while the smooth inner wall conforms easily to the residual limb. The Smart Seal Liner has a new seamless knitted construction with a modern look and is available in locking and cushion suspension. The locking version features a new distal construction to control distal distraction.



HIGH DENSITY  
(HD) GEL



LOCKING  
3.0 OR 6.0 MM  
UNIFORM THICKNESS



CUSHION  
3.0 OR 6.0 MM  
UNIFORM THICKNESS

## TOP FEATURES



Seamless knitted  
fabric



Innovative single  
piece construction



Offered with or without  
distal attachment




#makinglivesbetter




# CROSS SECTION DIAGRAM

## 3.0MM UNIFORM




## 6.0MM UNIFORM



## HOW TO SIZE

Measurements taken  
6cm from the distal end



MEASURED  
SIZE (CM)



SAFR - CUSHION  
3.0MM or 6MM UNIFORM

26-27 cm	SAFR <b>26</b> (3 or 6)
28-31 cm	SAFR <b>28</b> (3 or 6)
32-34 cm	SAFR <b>32</b> (3 or 6)
35-37 cm	SAFR <b>35</b> (3 or 6)
38-43 cm	SAFR <b>38</b> (3 or 6)

MEASURED  
SIZE (CM)



SADT - LOCKING  
3.0MM or 6MM UNIFORM

20-23 cm	SADT <b>20</b> (3 or 6)
24-25 cm	SADT <b>24</b> (3 or 6)
26-27 cm	SADT <b>26</b> (3 or 6)
28-31 cm	SADT <b>28</b> (3 or 6)
32-37 cm	SADT <b>32</b> (3 or 6)
38-43 cm	SADT <b>38</b> (3 or 6)

MEASURED  
SIZE (CM)



SBFR - CUSHION  
3.0MM or 6MM UNIFORM

20-23 cm	SBFR <b>20</b> (3 or 6)
24-25 cm	SBFR <b>24</b> (3 or 6)
26-27 cm	SBFR <b>26</b> (3 or 6)
28-31 cm	SBFR <b>28</b> (3 or 6)

## PRODUCTS OFTEN USED WITH SMART SEAL



VACUUM  
INTEGRATED  
PUMP (VIP)



## SKIN RELIEVER (ENCP)

Use the Skin Reliever (ENCP) with the Smart Seal to compensate for volume fluctuations with continued use of same socket.

MEASURED  
SIZE (CM)

ENCP  
TAPERED 3.0MM-1.5MM

10-19 cm	ENCP <b>16</b>
20-27 cm	ENCP <b>20</b>
28-37 cm	ENCP <b>28</b>



Tel +420 377 223 127 | Fax +420 377 223 010

[www.easyliner.eu](http://www.easyliner.eu) | [info@easyliner.eu](mailto:info@easyliner.eu)

Božkovské náměstí 17/21, 32600 Plzeň – Czech Republic

MAKING  
LIVES  
BETTER